



Dark-field condensers

Table 40

Designation	N.A.	Focal length mm	Object distance mm	For objectives of N.A.	Catalog No.
Ultracondenser, 1.2 ... 1.4 N.A., oil	1.2 - 1.4	5.9	1.1 - 1.3	0.75 - 1.0	46 55 00
Dry dark-field condenser, 0.8 ... 0.95 N.A.	0.8 - 0.95	8.2	6	0.6 - 0.75	46 55 05
Dry dark-field condenser, 0.7 ... 0.85 N.A.	0.7 - 0.85	8.5	6.5	0.4 - 0.6	46 55 06
For our microscopes with centering carrier, each of these condensers must be equipped with a condenser holder Z,					46 55 42.
For insertion into a condenser sleeve,					
the ultracondenser must be equipped with the centerable condenser holder S					46 55 41.
the other condensers with the condenser holder S					46 55 40.